

Duo™ II.I

Technical datasheet



Dispense Flow Rate	≥2 L/min
Water Quality (at 25° C)	18.2MΩ cm
Pressure	0.1 - 6 bar
Conductivity	<2000 µS/cm
Temperature	5 - 40°C
Free Chlorine	< 3 ppm
pH Value	4 - 10
Dimensions (H x W x D)	500 x 490 x 290 mm / 19.7" x 19.3" x 11.5"
Installed Weight	30 kg
Power Supply	100 - 240 V; 50/60 Hz
Silt Density Index	< 12 SDI